

SMA and Reverse Polarity SMA Specifications

Materials			
Connector Part	Material	Finish	
Bodies	Brass	Nickel or Gold	
	Stainless Steel	Passivated or Gold	
Center contact	Male: Brass	Gold	
	Female: Beryllium Copper		
Insulator	PTFE	N/A	
Crimp ferrule	Annealed Copper	Nickel or Gold	

Electrical			
Electrical Data	Detail		
Impedance	50 ohm		
Frequency range	Flexible cable: 0~12.4GHz		
	Semi-rigid cable: 0~18GHz		
Working voltage	RG402 (.141") » 500 volts rms max.		
	RG405 (.085") » 335 volts rms max.		
	RG58, 141, 142, 223/U » 500 volts rms max.		
	RG174, 188, 316/U » 335 volts rms max.		
	RG178, 196/U » 250 volts rms max.		
Insulation resistance	5,000 megaohms min.		
Dielectric withstanding voltage	RG402 (.141") » 1,000 volts rms max.		
	RG405 (.085") » 750 volts rms max.		
	RG58, 141, 142, 223/U » 1,000 volts rms max.		
	RG174, 188, 316/U » 750 volts rms max.		
	RG178, 196/U » 500 volts rms max.		
Contact resistance	Center contact: 3.0 milliohms max.		
	Outer contact: 2.0 milliohms max.		
VSWR: f(GHz)		Straight	Right angle
	RG178/U	1.20+0.025f	1.20+0.03f
	RG174, 316/U	1.15+0.02f	1.15+0.03f
	RG58, 141, 142, 223/U	1.10+0.01f	1.15+0.02f
	RG402 (.141")	1.05+0.005f	1.15+0.15f
	RG405 (.085")	1.05+0.005f	1.18+0.15f
Insertion loss	0.04dB max. x $\sqrt{f}$ GHz (straight)		
	0.06dB max. x $\sqrt{f}$ GHz (right angle)		

Mechanical

Mechanical Data	Detail
Engagement force	60lbs min.
Disengagement force	15 inch-pound
Connector durability	500 cycles min.
Cable retention force	RG58, 141, 142, 223/U » 40lbs min.
	RG174, 188, 316/U » 20lbs min.

Environmental

Environmental Data	Detail
Corrosion (salt spray)	MIL-STD-202 METHOD 101 TEST CONDITION B
Thermal shock	MIL-STD-202 METHOD 107 TEST CONDITION B
Vibration	MIL-STD-202 METHOD 204 TEST CONDITION D
Mechanical shock	MIL-STD-202 METHOD 213 TEST CONDITION I
Temperature Range	-65°C to 165°C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Linx Technologies:

[CONSMA001](#) [CONREVSMA015-R58](#) [CONREVSMA004](#) [CONREVSMA005-R178](#) [CONREVSMA014-R178](#)
[CONREVSMA014-R58](#) [CONREVSMA011-R58](#) [CONREVSMA003.031-L](#) [CONREVSMA008](#) [CONREVSMA007](#)
[CONREVSMA013.062](#) [ADP-RPSM-SMAF](#) [CONSMA015](#) [CONSMA005](#) [CONSMA005-R178](#) [CONSMA008](#)
[CONSMA007](#) [CONSMA007-R178](#) [CONSMA007-R58](#) [CONSMA012](#) [ADP-SMAM-SMAM](#)