


- Samples can deviate in the execution from the serie.



Tab material: Isotan (54%Cu,44%Ni,Mn)

All framed values will be used for dimension checking !

- Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely

Rev.	☐			Rev.	☐				Customer's Approval			
Rev.	☐			Rev.	☐				Date			
Rev.	☐			Rev.	☐				Signature			
Titel: CR2430SM								Scale 2:1	Drawn	05.11.07	SRi	
									Checked	06.11.07	BBö	
									Approved			
renata batteries								CH-4452 Itingen Switzerland		3.9205.4-		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renata:](#)

[CR2430SM](#)