

285 Flux-Cored Wire Mildly Activated Rosin Cored Wire for Leaded and Lead-free Alloys

Product Description

Kester 285 mildly activated rosin flux is classified as Type ROL0 flux under IPC J-STD-004. This flux was formerly classified as Type RMA per QQ-S-571. 285 consists of high quality, purified rosin to which a synergistic combination of activating agents has been incorporated. The fluxing ability of 285 is much greater than ordinary mildly activated rosin fluxes and is comparable to fully activated rosin fluxes. 285 has been developed for use in the electronic industry where difficult assemblies are to be soldered, but process requirements stipulate use of a mildly activated rosin flux.

Performance Characteristics:

- Industry standard RMA cored wire
- Compatible with leaded and lead-free alloys
- Classified as ROL0 per J-STD-004



RoHS Compliance

This product meets the requirements of the Restriction of Hazardous Substances (RoHS) Directive, 2011/65/EU for the stated banned substances. (Applies only if this core flux is combined with a lead-free alloy)

Reliability Properties

Copper Mirror Corrosion: Low Tested to J-STD-004, IPC-TM-650, Method

Corrosion Test: Low

Tested to J-STD-004, IPC-TM-650, Method 2 6 15

Silver Chromate: Pass

Tested to J-STD-004, IPC-TM-650, Method 2.3.33

Chloride and Bromides: None

Detected

Tested to J-STD-004, IPC-TM-650, Method 2.3.35

Fluorides by Spot Test: Pass Tested to J-STD-004, IPC-TM-650, Method 2.3.35.1

SIR, IPC (typical): Pass

Tested to J-STD-004, IPC-TM-650, Method 2.6.3.3

	Blank	285
Day 1	1.0*10 ¹⁰ Ω	3.2*10 ⁹ Ω
Day 4	9.5*10° Ω	7.7*10 ⁹ Ω
Day 7	8.3*10° Ω	7.0*10 ⁹ Ω

Spread Test (typical): Pass Tested to J-STD-004, IPC-TM-650, Method 2 4 46

	Area of Spread mm ² (in ²)	
Flux Core Solder	Cu	Ni
285	335 (0.52)	140 (0.22)
282	240 (0.37)	100 (0.16)
44	280 (0.43)	160 (0.25)

Application Notes





285 is available in a wide variety of alloys, wire diameters and flux percentages. For most applications, Sn63Pb37 or Sn96.5Ag3.0Cu0.5 is used. Consult Kester's website for the comprehensive alloy list and for standard wire diameters. The standard wire diameter for most applications is 0.8mm (0.031"). Wire diameters range from 0.25-6.00mm (0.010-0.250in). The amount of flux in the wire dictates the ease of soldering for an application. 285 is packaged on spools of different sizes to accommodate a variety of applications.

Note: Core Size 50, 58 and 66 = 1.1%, 2.2% and 3.3% flux core.



Solder iron tip temperatures are most commonly between 315-371°C (600-700°F) for Sn63Pb37 and Sn62Pb36Ag02 alloys and 371-427°C (700-800°F) for lead-free alloys. Heat both the land area and component lead to be soldered with the iron prior to adding 285 cored wire. Apply the solder wire to the land area or component lead. Do not apply the wire directly to the soldering iron tip. If needed, Kester 186 and 186-18 Mildly Activated Rosin Flux may be used as a compatible liquid flux to aid in reworking soldered joints. Kester 186 Mildly Activated Rosin Flux is also available as a Flux-Pen® for optimum board cleanliness.

Cleaning

285 flux residues are non-corrosive, non-conductive and do not require removal in most applications.

Storage and Shelf Life

Storage must be in a dry, non-corrosive environment. The surface may lose its shine and appear a dull shade of grey. This is a surface phenomena and is not detrimental to product functionality. Flux cored solder wire has a limited shelf life determined by the alloy used in the wire. For alloys containing > 70% lead, the shelf life is two years from date of manufacture. Other alloys have a shelf life of three years from date of manufacture.

This product, during handling or use, may be hazardous to your health or the environment. Read the Safety Data Sheet (SDS) and warning label before using this product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kester:

24-6337-9721 24-1585-9711 24-6040-9702 24-6040-9703 24-6040-9709 24-6040-9711 24-6040-9713 24-6040-9715 24-6040-9718 24-6040-9720 24-6040-9721 24-6040-9759 24-6337-9628 24-6337-9706 24-6337-9711 24-6337-9715 24-6337-9716 24-6337-9717 24-6337-9735 24-6337-9744 24-6337-9746 24-6337-9756 24-6337-9758 24-7050-9702 24-7050-9703 24-7050-9709 24-7050-9710 24-7050-9711 24-7050-9718 24-7050-9727 24-7068-9710 24-7068-9720 24-7080-9702 24-7080-9703 24-7080-9710 24-7080-9713 24-7080-9715 24-7080-9718 24-7150-9702 24-7150-9710 24-7317-9700 24-7317-9710 24-7317-9713 24-7317-9716 24-7317-9718 24-7317-9727 24-7340-9700 24-7340-9713 24-7340-9700 24-7340-9713 24-7040-9718 24-7050-9718 24-7050-9744 26-6337-9711 91-6337-9703 91-6337-9727 92-6337-9702 92-6337-9710 92-6337-9711 92-6337-9713 92-6337-9717 92-6337-9718 92-6337-9728 92-6337-9756 92-7150-9702 92-7150-9703